

bottelpack®

bp 460


20 moulds



ASEPTIC BLOW-FILL-SEAL PACKAGING MACHINE

for the production of ampoules


bp 460-20		volume max. (ml)	max. container width ¹ (mm)	capacity ² (approx. pieces/h)
10-cavities	multi	8	28	12,400
	single	8	24	
12-cavities	multi	8	23	14,900
	single	8	20	
14-cavities	multi	8	20	17,400
	single	8	17	
15-cavities	multi	8	18	18,600
	single	8	15	
16-cavities	multi	5	17	19,850
18-cavities	multi	5	15	22,300
20-cavities	multi	4	13	26,700
22-cavities	multi	4	11.5	29,300
24-cavities	multi	3	10	32,000
25-cavities	multi	2	10	33,300

¹x = max. container width

²Capacity indications subject to:
type of plastic, shape of ampoule,
weight of ampoule, nature of filling liquid

multi = multiblock
single = individual ampoule

FILLING YOUR NEEDS



TECHNICAL DATA

MOULDS:

- Number of moulds: 20
- Height: 76 mm
- Standard volumes: 0.2 ml up to 20 ml
- Larger volumes on request

POWER:

- 3/N/PE AC 400 V 50 Hz oder 60 Hz

EXTRUDER:

- KP55-24D

ELECTRICAL SUPPLY:

- Approx. 65 kW

Ø CONSUMPTION:

- Approx. 35 kW

COMPRESSED AIR:

- Average consumption approx. 600 NL/min in oil-free quality
- Operation pressure 8 bar minimum

COOLING WATER (closed cycle cooling):

- Approx. 2.5 m³/h with 10 – 12 °C and 4 – 5 bar, dirt-filtered ≤ 55 micron

CITY WATER CONSUMPTION:

- Approx. 60 l/h with max. 20 °C and 4 – 5 bar, dirt-filtered ≤ 55 micron

STEAM:

- Pure steam 2.5 bar, particle-filtered ≤ 1 micron (DIN58950-7)
- Consumption at sterilization: approx. 40 kg/h

DOSING:

- Time-pressure-dosing continuously adjustable for each single cavity with filling volumes between 0.1 ml and 30 ml

EXTRUDER:

- Extruder with continuously regulable electric drive
- Screw Ø 55 – 24D melting capacity up to max. 80 kg/h
- The melting capacity refers to polyethylene LDPE up to 0.93 density – other plastics may vary

EXTRUSION HEAD:

- Oval parison head

WEIGHT OF MACHINE:

- Approx. 13 tons

SOIL BEARING VALUE:

- Approx. 1 ton/m²

EXTRA AND SPECIAL EQUIPMENT:

- **coolBFS** to fill heat sensitive products
- Integrated circulation function to fill suspensions
- Laser system for container coding and separation
- And many other customer specific options

Technical data and dimensions depend on the final project specifications and are subject to change.

Rommelag Kunststoff-Maschinen Vertriebsgesellschaft mbH
Mayenner Straße 18 – 20 · 71332 Waiblingen · Germany
T +49 7151 95811-0 · F +49 7151 15526 · mail.rd@rommelag.com · www.rommelag.com

Rommelag USA, Inc.
27905 Meadow Drive · Suite 9 · Evergreen · CO 80439 · USA
T +1 303 674 8333 · F +1 303 670 2666 · www.rommelag.com

Rommelag AG
Fabrikweg 16 · 5033 Buchs · Switzerland
T +41 62 834 55 55 · F +41 62 834 55 00 · mail.rch@rommelag.com · www.rommelag.com

Rommelag Trading (Shanghai) Co., Ltd.
Room 905-906, Building B, Greenland Center, No.600 Longhua Middle Road
Xuhui District · 200032 Shanghai · P.R. China
T +86 22 1633 588 81 · F +86 21 6335 8883 · www.rommelag.com